

# TOP Wavelengths

## DFB: High-Power 4565 nm



### TOP WAVELENGTH

- 760.8 nm
- 1278.8 nm
- 1392.0 nm
- 1512.2 nm
- 1560 - 1590 nm
- 1651 & 1654 nm
- 1742.0 nm
- 1854 & 1877 nm
- 2004.0 nm
- 2330 & 2334 nm
- 3240 & 3270 nm
- 3345 nm HP
- 3345 & 3375 nm
- 4524 & 4534 nm
- 4565 nm HP**
- 5184 & 5263 nm

nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For 25 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

### Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14  $\mu$ m**.

Our excellent **spectral purity** is characterized by a large side mode suppression ratio (**SMSR**) of **> 35 dB**, giving your system a low signal to noise ratio against crossinterference.


A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

**Fast and wide wavelength tuning** is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very **large tuning coefficient**.

**“Do not change your ideas, let us deliver the laser that fits your application.”**

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.




TO66 with TEC and NTC,  
sealed with cap and AR  
coated window

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**




# Superior Specifications: High-Power 4565 nm




This data sheet reports performance data of a **sample nanoplus High-Power DFB laser at 4565 nm with enhanced specifications.**

Standard specifications are available at: [nanoplus.com/DFB/4000nm-4600nm](https://nanoplus.com/DFB/4000nm-4600nm).

These lasers are particularly suitable for nitrous oxide (N<sub>2</sub>O) and carbon monoxide (CO) detection.



Typical room temperature cw spectrum  
of a nanoplus DFB ICL at 4565 nm



Typical mode hop free tuning of a nanoplus  
DFB ICL at 4565 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typical	max.
operating wavelength (at $T_{op}$ , $I_{op}$ )	$\lambda_{op}$	nm		4565	
optical output power (at $\lambda_{op}$ )	$P_{op}$	mW		15	
operating current	$I_{op}$	mA			120
operating voltage	$V_{op}$	V		5	
threshold current	$I_{th}$	mA	20	30	40
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	$C_I$	nm / mA		0.12	
temperature tuning coefficient	$C_T$	nm / K		0.45	
operating chip temperature	$T_{op}$	°C	+15	+20	+40
operating case temperature*	$T_c$	°C	-20	+25	+55
storage temperature*	$T_s$	°C	-30	+20	+70

\* non-condensing

## packaging

**TO66 with TEC and NTC, black cap, AR coated window**

**Other packaging options may be discussed on request.**

Technical drawings & accessories are available at: [nanoplus.com/packaging](https://nanoplus.com/packaging)

Please contact [sales@nanoplus.com](mailto:sales@nanoplus.com) for customized specifications, quotes and further questions.  
Visit our website for technical notes, application samples or literature referrals.